

Instructions:

1. All membranes are tested strictly and treated with 1.0% NaHSO<sub>3</sub> for storage (propylene glycol antifreeze is added in winter). We adopt vacuum packaging and the hard cardboard is used for packaging to prevent the growing of microbial in short-term storage and transport. The protect liquid of 1.0% NaHSO<sub>3</sub> is promoted (confected with RO pure water) to marinate components
2. We recommend that you drain the first hour of pure water
3. Any chemical medicament, having a bad effect on membrane's performance, is bidden to add in the period of storage, installation and normal function. While installing, please use pure water or glycerine if lube is needed
4. FRP (Fibreglass-Reinforced Plastics) is adopted for 4040 and 8040 and the limited pressure is 15 psi. Adhesive tape wrap is adopted for household membrane and pyrocondensation film is added for other dimensions of membranes
5. All membranes adopt the universal standards of international size and can interconvert with all types of membranes. Presently .25 series adopts the pressure vessel whose diameter is 2.5inches, 40 series is 4.0 inches and 80 series is 8.0 inches